

CAPE TOOLS

est. 1962 & JEWELLERY SUPPLIES

ENGRAVING MACHINERY & PRECISION TOOLS

- Specially designed for **fixed time tumbling (0-60 minutes)**.
- **Auto-reverse function** enables thorough tumbling.
- With **4 variable speed control** so that jewellery can be polished with good care.



SETUP

1. Prepare your barrel & remove the lid.
2. Add steel media to the barrel within the max capacity.
3. Add your workpieces; using 1 part workpiece to 6 parts media volume.
4. Add your compound solution to the barrel & cover media with water by 2cm.
(Follow instructions on the label of the compound to mix the solution properly)
5. Secure the lid onto the barrel & position the barrel between roller guides.
6. Position the barrel between roller guides & start tumbling.
7. Use tumbler for no more than 120 minutes. (Barrel should never weigh more than 4kg)
8. Rinse the workpieces, stainless steel shot & the tumbler barrel.

Weight	18kg
Capacity	11kg
Voltage	220V - 110V
Dimension	570 x 210 x 390mm

**These tumblers come fully assembled.
Simply place the tumbler base on a
sturdy, level work surface.**